

Polariscope

LSM-V50

Advanced strain measurement for
glass and plastic products.



Improved Light Source

Improved light source ensures uniform observation without unevenness.




LSM-4401LE(Previous Model)

New




LSM-V50



LSM-4401LE(Previous Model)

New



LSM-V50

Retardation Standard Plate

Included for daily calibration and comparative evaluation.



Custom combinations of specific retardation values are available as a special order. Please contact us for details


Enhanced Usability

Designed for horizontal use to support your measurement needs.

An extended-column model is available as an option for inspecting taller samples.



【 Designed for horizontal use 】



【 Standard height 】



【 With extended-column 】

Product Specifications

Model Name	LSM-V50
Size(body)	W285 × D365 × H380 mm
Weight	6kg
Measurement area size	205 × 205mm
Inspection Method	Crossed Nicols/Sensitive Color/ Senarmont Method
Sample Space (Height)	55mm – 288mm (Standard) / 400mm – 638mm (With extension pillar)
Power Supply Voltage	AC100-240V 50/60Hz

株式会社 ルケオ  luceo co.,ltd.

30-9 Ohyamakanai-cho, Itabashi-ku,
Tokyo, 173-0024
TEL +81-3-3956-4111 FAX +81-3-3956-2335
URL <https://luceo.co.jp/en/>